







P.C.B LAYOUT



螺丝规格

零件 编号	X尺寸	内牙
5	4.8	4#40
6	5.8	4#40

UNLESS OTHERWISE SPECIFIED TOLERANCE			DRAWN NAME:		
ANG.	±5°		VGA/DB 15PIN 母座 直插3排脚 锁螺丝		
	0.	±0.5			
	.00	±0.3			
SCALE: AS SHOWN	UNIT: mm	±0.2			

深圳市连欣科技有限公司

DRAWN WAN				25/12/14		PART NO:	
CHECKED CHEN				25/12/14		XDDB-1510-1445B06	
APPROVED CHEN				25/12/14		DWG NO:	
DATE				SIZE A4		VGA201412250007	
REV.				REV. A			

- 说明:
- 1.特性:
- 额定电压 :250V AC最大值
 - 额定电流 :最大3A
 - 接触阻抗 :30mΩ MAX
 - 绝缘阻抗 :3000MΩ MIN. at 500V DC
 - 耐电压值 :250V AC RMS for 1Minute
 - 工作温度 : -45℃~+85℃
- 2.材料:
- 胶 芯 : PBT rated
 - 端 子 : 铜合金
 - 外 壳 : 铁合金/铜合金/不锈钢
 - 铜 柱 : 铜合金, 镀锡
 - 螺 丝 : 铁棒/铜合金, 镀镍