








1 2 3 4 5 6 7 8 9 10

RoHS



- Note:
1. Material:
- 1.1 Housing: High temperature thermoplastic with g.f.U.L94V-0
 - 1.2 Contact: copper alloy, t=0.25mm
 - 1.3 Shell: copper alloy, t=0.40mm
2. Specification:
- 2.1 Current rating: 1 A Max.
 - 2.2 Dielectric withstanding voltage: 100 V(ac) for 1 min.
 - 2.3 Contact resistance: 50 mW Max.
 - 2.4 Insulation resistance: 100 MW Min.
 - 2.5 Total mating force: 3.57 Kgf Max.
 - 2.6 Total unmating force: 0.71 Kgf Min.
 - 2.7 Temperature range: -25°C~85°C

产品图

深圳市精拓金电子有限公司
Shenzhen Jing Tuo Jin Electronics Co., Ltd.

PRODUCT CHART DWG

公差一览表

TOLERANCE UNLESS OTHERWISE

UNIT

MM

SCALE

DATE

DATE

DATE

单位

MM

比例

1:1

日期

2021-03-10

制图

L-S-S

审核

郭治雷

核准

黄国荣

制图料号

920-462A2021S10119

产品名称

MINI/SP四脚全贴片距5.45

Product NO.

LCP黑胶无柱SMT贴片泰拉卷盘

角法

角法

版本

版本

角法

角法

您正在使用 ZWCAD 2022 个人版, 不得用于商业用途, 详情请咨询 4007-182-588.