




目錄 MAPX	變更內容 MODIFICATION	日期 DATE
------------	----------------------	------------



- NOTES:
- Housing: Thermoplastics
 - Contact: Copper Alloy
 - Shell: Copper Alloy/Steel
 - Voltage Current Rating: 1.5 AMP. 30V AC
 - Insulation Resistance: 1000MΩ Min.
 - Contact Resistance: 30 MΩ Max.
 - Dielectric Withstanding Voltage: 500W AC
 - Temperature Range: -35°C to +85°C
 - Insulator color: Black/White
 - Plastic material: PBT/LCP/Others
 - Shell finish: Nickel plated/Tin-Lead plated
 - Mechanical:
 - Mating Force: 3.5KG MAX
 - Umating Force: 1.02 KG MIN.
 - Contact finish:
 - 01: Selective Gold Flash
 - 02: Selective Gold 3U"
 - 03: Selective Gold 5U"
 - 04: Selective Gold 15U"
 - 05: Selective Gold 30U"

产品图
PRODUCT CHART DWG

深圳市精拓金电子有限公司

公差一览表 TOLERANCE UNLESS OTHERWISE		单位 UNITS	MM	制图 DRAWING	Z-V-B	产品料号 PRODUCT PART NO.	903-241A2021S10210
X	±0.25	X'	±.5'	比例 SCALE	1:1	产品名称 PRODUCT NAME	AF无后盖直脚无边内弹14.0铁壳T型LCP黑胶SMT/单格吸塑
.XX	±0.15	.XX'	±.1'	日期 DATE	2015.08.14	审核 CHECK	郭治富
.XXX	±0.10	.XXX'	±0.5'	核准 APPRO		黄国荣	
				角法 VIEW		版本 VER	A0

