

1 ROHS

2

3

4

5

6

7

8

9

10

MAPX	MODIFICATION	DRW	DATE


Specifications / 技术规格:

Current rating: 2A  
 额定电流: 2A  
 Voltage rating: 250V AC, DC  
 额定电压: 250V AC, DC  
 Insulation Resistance: 1000MΩ Min.  
 绝缘电阻: 最小1000MΩ  
 Dielectric Withstanding: 800V AC 1Min  
 耐压: 800V AC 1分钟  
 Contact Resistance: 20mΩ Max.  
 接触电阻: 最大20mΩ  
 Operating Temperature: -25°C to +85°C  
 工作温度: -25°C 到85°C

Materials / 材料:

Contact Material: Brass(plating Sn)  
 接触端子材料: 黄铜(镀锡)  
 Insulation Material: PA66 UL94V-0/2  
 绝缘塑胶材质: PA66 UL94V-0/2

孔数	型号	尺寸 (mm)			
		A	B	C	D
2	PH-2AN	2.0	4.9	5.9	0.9
3	PH-3AN	4.0	6.9	7.9	1.9
4	PH-4AN	6.0	8.9	9.9	3.9
5	PH-5AN	8.0	10.9	11.9	5.9
6	PH-6AN	10.0	12.9	13.9	7.9
7	PH-7AN	12.0	14.9	15.9	9.9
8	PH-8AN	14.0	16.9	17.9	11.9
9	PH-9AN	16.0	18.9	19.9	13.9
10	PH-10AN	18.0	20.9	21.9	15.9
11	PH-11AN	20.0	22.9	23.9	17.9
12	PH-12AN	22.0	24.9	25.9	21.9
13	PH-13AN	24.0	26.9	27.9	23.9
14	PH-14AN	26.0	28.9	29.9	25.9
15	PH-15AN	28.0	30.9	31.9	27.9
16	PH-16AN	30.0	32.9	33.9	29.9



产品图

深圳市精拓电子有限公司  
 Shenzhen Jing Tuo Jin Electronics Co., Ltd.

公差一览表	UNIT	MM	制图号	920-36601011D10019
TOLERANCE UNLESS OTHERWISE	UNITS	MM	DRAWING	
±0.35 X	±5.°	1:1	审核	PH2.0-3P 直针白色
±0.25 X	±2.°	日期	核准	黄国荣
±0.20 XX	±1.°	DATE	APRD	版本
±0.05 XXX	±0.5°	2021-03-10		A0

您正在使用 ZWCAD 2022 个人版, 不得用于商业用途, 详情请咨询4007-182-588。