

MAPX	MODIFICATION	DATE
------	--------------	------

规格说明: Specifications:

电气特性: Electrical:

- 额定电流: Current Rating  
1.0A/contact terminal
- 额定电压: Voltage Rating  
30V DC
- 接触阻抗: Contact Resistance  
50 milliohms MAX
- 耐电压: Dielectric Withstanding Voltage:  
300 V AC AT Sea Level
- 绝缘阻抗: Insulation Resistance:  
100MEGA ohms MIN

物理性能: Mechanical:



- 插拔力: Connector Mate and Umate Force  
Mate force: 3.0kgf (MAX)  
Umate force: 0.7kgf (MIN)
- 端子保持力: Terminal Retention  
0.5kgf (MIN)

原材料: Material:

- 塑胶: Housing:  
Hing Temperature Thermoplastics,  
UL 94V-0 LCP Black
- 端子: Contact: Copper Alloy C5191
- 外壳: Shell: Copper Alloy C2680

电镀: Finish:

- 端子: Contact: Plated Gold in Mating Area;  
Tin On Solder Tails
- 外壳: Shell: Nickel Plating



RECOMMENDED PCB LAYOUT  
(TOL.: ±0.05)

产品图  
PRODUCT CHART DMC

公差一览表 TOLERANCE UNLESS OTHERWISE	
X	±0.15
.X	±0.10
.XX	±0.05
.XXX	±0.03

深圳市精拓金电子有限公司

单位 UNITS	MM	制图 DRAWING	邱建辉	制料号 PRODUCT PART NO.	920-154A2021S10101
比例 SCALE	1:1	审核 CHECK	郭治富	产品名称 PRODUCT NO.	MICRO SP B型有边四脚插板有柱DIP增高1.35LCP黑胶
日期 DATE	2013.12.23	核准 APPRO	黄国荣	角法 VIEW	版本 VER
					A0