



THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



* UNLESS OTHERWISE SPECIFIED TOLERANCES
ON DECIMAL IS: ANGLE $\pm 1^\circ$
UNIT: MM

BACKSHELL KIT INCLUDES:

- (2) BACKSHELL HALVES
- (2) JACKSCREW 4-40
- (2) SHELL SCREW
- (2) METAL CLAMP
- (4) CLAMP SCREW
- (2) BLANKING PLATE



DIMENSIONS(mm/in)

Size	A ^{±1.30 ±0.051}	B ^{±1.30 ±0.051}	C ^{±1.20 ±0.047}	D ^{±0.25 ±0.01}
9	31.00 1.221	41.40 1.630	15.00 0.591	24.99 0.984
15	40.30 1.587	45.20 1.780	15.00 0.591	33.32 1.312
25	53.50 2.106	45.20 1.780	15.00 0.591	47.04 1.852
37	70.00 2.756	45.20 1.780	15.00 0.591	63.50 2.500

ORDERING INFORMATION:

SIZE	P/N-KITTED	PRODUCT CODE
9-WAY	6550-0101-01	MHTRI-P-9-K
15-WAY	6550-0101-02	MHTRI-P-15-K
25-WAY	6550-0101-03	MHTRI-P-25-K
37-WAY	6550-0101-04	MHTRI-P-37-K

BACKSHELL MATERIAL:

JACKSCREW 4-40:

SHELL SCREW:

METAL CLAMP:

CLAMP SCREW:

BLANKING PLATE:

OPERATING TEMP:

ABS UL 94-HB RATED

STEEL -BLACK OXIDE FINISH

STEEL -BLACK OXIDE FINISH

STEEL -ZINC PLATED

STEEL -ZINC PLATED

ABS UL 94-HB RATED

-55°C TO +120°C



THIS SERIES FULLY CONFORMS TO THE
EUROPEAN UNION DIRECTIVES 2002/95/EC
AND 2002/96/EC FOR RoHS COMPLIANCY.



THESE DRAWINGS AND SPECIFICATIONS ARE THE
PROPERTY OF MH CONNECTORS AND SHALL NOT BE
REPRODUCED, COPIED OR USED AS THE BASIS FOR
THE MANUFACTURE OR SALE OF APPARATUS WITHOUT
WRITTEN PERMISSION.

**MH CONNECTORS ,
DIVISION OF EDAC**

DRAWN Johnny		DATE 11-24-15	
APPROVED Victor Lin		DATE 11-24-15	
SCALE 1 : 1	SHEET OF 1 OF 1		REV: 2.0
DRAWING No MHTRI-P-SERIES			