




THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



* UNLESS OTHERWISE SPECIFIED TOLERANCES
ON DECIMAL IS: ANGLE $\pm 1^\circ$
.X ± 0.25
.XX ± 0.15



PIN	A ± 0.25	B ± 0.25	C ± 0.25	D ± 0.25	E ± 0.25
09	30.81	24.99	16.33	19.28	15.50
15	39.25	33.32	24.66	27.55	24.75
25	53.03	47.04	38.38	41.25	38.00
37	69.40	63.50	54.85	57.40	54.20

Order Codes:
Socket Connector

9-WAY	2101-0190-11	MHDBC9SS
15-WAY	2101-0190-12	MHDBC15SS
25-WAY	2101-0190-13	MHDBC25SS
37-WAY	2101-0190-14	MHDBC37SS

Remark:

1.SPECIFICATION:

Rated voltage:250V
Rates current:3AMP
Contact resistance:30M Ω MAX
Insulation resistance:1000M Ω MIN.at 500V DC
Withstand voltage:500V Per mintute
Temperature range:-55 -105 $^\circ$ C

2.MATERIAL:

Plastic:PBT+30% G.F (UL94V-0) BLACK
Spcc shell:Spcc front shell is nickel plated back shell is nickel plated

THESE DRAWINGS AND SPECIFICATIONS ARE THE
PROPERTY OF MH CONNECTORS AND SHALL NOT BE
REPRODUCED, COPIED OR USED AS THE BASIS FOR
THE MANUFACTURE OR SALE OF APPARATUS WITHOUT
WRITTEN PERMISSION.

DRAWN
Iven Ou
DATE
08-30-22

APPROVED
DATE

SCALE
1 : 1
SHEET OF
1 OF 1
REV:
4.0

DRAWING No
MHDBCXX SS



THIS SERIES FULLY CONFORMS TO THE
EUROPEAN UNION DIRECTIVES 2002/95/EC
AND 2002/96/EC FOR RoHS COMPLIANCY.



MH CONNECTORS ,
DIVISION OF EDAC