



THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.

BACKSHELL KIT INCLUDES:

- (2) BACKSHELL HALVES
- (1) GROMMET
- (2) JACKSCREWS
- (2) SHELLSCREWS
- (2) CLAMPSCREWS
- (1) METAL CLAMP
- (1) METAL CLAMP FLAT

MHDM9-DB9S-K=MHDM9-K+ MHDB9SS
MHDM15-DB15S-K=MHDM15-K+ MHDB15SS
MHDM25-DB25S-K=MHDM25-K+ MHDB25SS
MHDM37-DB37S-K=MHDM37-K+ MHDB37SS



BACKSHELL MATERIAL:
PLATING:
GROMMET:
COLOR
SCREW:
CLAMP:
OPERATING TEMP:

DIE CAST ZINC ALLOY
NICKEL PLATED
THERMOPLASTIC ABS
NATURAL NICKEL PLATED
STEEL, ZINC PLATED
STEEL, SHEET, NICKEL PLATED
-40°C TO +120°C



THIS SERIES FULLY CONFORMS TO THE
EUROPEAN UNION DIRECTIVES 2002/95/EC
AND 2002/96/EC FOR RoHS COMPLIANCY.



THESE DRAWINGS AND SPECIFICATIONS ARE THE
PROPERTY OF MH CONNECTORS AND SHALL NOT BE
REPRODUCED, COPIED OR USED AS THE BASIS FOR
THE MANUFACTURE OR SALE OF APPARATUS WITHOUT
WRITTEN PERMISSION.

MH CONNECTORS ,
DIVISION OF EDAC

* UNLESS OTHERWISE SPECIFIED TOLERANCES
ON DECIMAL IS: ANGLE $\pm 1^\circ$
UNIT: MM .XX ± 0.50

DIMENSIONS(mm/in)					
SIZE	A $\pm_{0.012}^{0.30}$	B $\pm_{0.020}^{0.50}$	C $\pm_{0.010}^{0.25}$	D $\pm_{0.051}^{1.3}$	E
9	41.3	15.4	24.99	32.2	13.0
	1.626	0.606	0.984	1.268	0.512
15	43.3	15.4	33.32	40.6	13.0
	1.705	0.606	1.312	1.598	0.512
25	49.5	15.4	47.04	54.5	13.0
	1.949	0.606	1.852	2.146	0.512
37	54.3	15.4	63.50	70.7	13.0
	2.138	0.606	2.500	2.783	0.512

ORDERING INFORMATION: WITH "MH" LOGO

SIZE	P/N - KITTED	PRODUCT CODE
9-WAY	6560-0136-01	MHDM9-K
15-WAY	6560-0136-02	MHDM15-K
25-WAY	6560-0136-03	MHDM25-K

ORDERING INFORMATION: WITHOUT "MH" LOGO

SIZE	P/N - KITTED	PRODUCT CODE
9-WAY	6560-0136-01	MHDM9-NL-K
15-WAY	6560-0136-02	MHDM15-NL-K
25-WAY	6560-0136-03	MHDM25-NL-K
37-WAY	6560-0136-04	MHDM37-K

NOTE: SIZE 37 WAY ONLY HAS NON-LOGO .

DRAWN Johnny		DATE 11-24-15	
APPROVED Victor Lin		DATE 11-24-15	
SCALE 1 : 1	SHEET OF 1 OF 1	REV 4.0	
DRAWING No MHDM-XX-K			

