




THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



* UNLESS OTHERWISE SPECIFIED TOLERANCES
ON DECIMAL IS: ANGLE $\pm 1^\circ$
UNIT: MM .XX ± 0.35

- BACKSHELL KIT INCLUDES:
- (2)BACKSHELL HALVES
 - (3)4-40 THUMBSCREWS
 - (2)CLAMP SCREWS
 - (2)CLAMP
 - (1)BLANKING PLUG



DIMENSIONS(mm/in)				
SIZE	A $\pm 1.6(+.063)$ $-.50(-.02)$	B $\pm 1.1(+.043)$ $-.50(-.02)$	C $\pm .80(+.032)$ $-.50(-.02)$	D $\pm .50$ $\pm .02$
9	31.5	40.0	15.00	24.99
	1.240	1.575	0.591	0.984
15	40.0	40.0	15.00	33.32
	1.575	1.575	0.591	1.312
25	53.5	43.0	15.00	47.04
	2.106	1.693	0.591	1.852

ORDERING INFORMATION:

SIZE	P/N – KITTED	PRODUCT CODE
9-WAY	6260-0107-01	MHDSSK-P-9-L-K
15-WAY	6260-0107-02	MHDSSK-P-15-L-K
25-WAY	6260-0107-03	MHDSSK-P-25-L-K

BACKSHELL MATERIAL: ABS,UL RECOGNIZED BLACK
JACKSCREWS: STEEL:ZN PLATED WITH PLASTIC KNOB
MATING SCREW: STEEL:ZN PLATED
BLANKING PLUG: ABS,UL RECOGNIZED
CLAMP SCREW: STEEL:ZN PLATED
METAL CLAMP: STEEL:ZN PLATED
PLASTIC CLAMP: ABS,UL RECOGNIZED
OPERATING TEMP: -55°C TO+110°C

THESE DRAWINGS AND SPECIFICATIONS ARE THE
PROPERTY OF MH CONNECTORS AND SHALL NOT BE
REPRODUCED, COPIED OR USED AS THE BASIS FOR
THE MANUFACTURE OR SALE OF APPARATUS WITHOUT
WRITTEN PERMISSION.

DRAWN Johnny		DATE 11-24-15
APPROVED Victor Lin		DATE 11-24-15
SCALE 1 : 1	SHEET OF 1 OF 1	REV: 3.0
DRAWING No MHDSSK-P-XX-L		



THIS SERIES FULLY CONFORMS TO THE
EUROPEAN UNION DIRECTIVES 2002/95/EC
AND 2002/96/EC FOR RoHS COMPLIANCY.



MH CONNECTORS ,
DIVISION OF EDAC