





FCIconnect.com

Copyright FCI



PC card drilling dimensions(after plating)
(thickness $1.60\pm 0.20\text{mm}$)



LF FOR LEAD FREE



SHELL	PART NUMBER	DESIGNATIONS
09	D09P13A*G*00**	HEADER 9 CTS RIGHT ANGLED-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
15	D15P13A*G*00**	HEADER 15 CTS RIGHT ANGLED-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
25	D25P13A*G*00**	HEADER 25 CTS RIGHT ANGLED-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
37	D37P13A*G*00**	HEADER 37 CTS RIGHT ANGLED-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.

4 = Performance level PL3 ≥ 200 OPERATIONS

6 = Performance level PL1 ≥ 500 OPERATIONS

I =SCREWLOCK Threaded M3

V =SCREWLOCK Threaded UNC 4.40 sellers

mat'l. code SEE.NOTES				surface ISO 1302		tolerance ISO 406 ISO 1101		projection 		product family DELTA-D										
ltr	ecn no	dr	date	tolerances unless otherwise specified		angles		linear		MM 		title MALE DELTA-D RIGHT ANGLED		WITH SCREW LOCK, HARPOON & METAL BRACKET						
D	I05-0124	JS	2005/07/27					0.X± 0.1												
E	I06-0074	SK	2006/06/08					0.XX± 0.1												
F	I09-0023	AS	2009/02/11	X±1°				0.XXX± 0.1		scale 1:1										
G	ELXI-I-15060	AB	2013/06/25	dr	GEORGE.V.J		2006/10/17				dwg no				sheet 1 of 1				size 5	
-	-	-	-	engr	ALIAS.BABU		2013/06/25				C01-8646-0742				A3					
-	-	-	-	chr	MITHUN.PAUL		2013/06/25													
-	-	-	-	appd	BIJU.K.PAUL		2013/06/25													
sheet index		revision		G	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
		sheet		1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	D