

NT1620SP

简易规格书

苏州纽特捷光电科技有限公司



手持式二维条码扫描器

HandHeld 2D Barcode Scanner

开票功能：支持支付宝开票功能，方便您的使用

更流畅的手机支付条码的阅读能力：支持支付宝，微信支付功能

开机迅速，即插即用

手持式二维条码扫描器

HandHeld 2D Barcode Scanner

物理特性/Physical Characteristics

尺寸 Dimensions : 156.2mm x 68mm x 109.2mm

重量 Weight : 115.5g

电压 Voltage : 5V

开机电流 Starting Current : 112mA

待机电流 Stand-by Current : 75.8mA

工作电流 Work Current : 136mA

性能指标/Performance Characteristics

传感器像素 Image (Pixels) : 640 pixels (H) x 480 pixels (V)

光源 Light Source : (Aimer) Red color LED; (Illumination) White color LED

视场角 Field of View : 28°(Horizontal) , 20°(Vertical)

旋转倾斜偏转 Roll / Pitch / Yaw : 360°, ±65°, ±65°

打印对比度 Print Contrast : 20% minimum reflective difference

接口支持 Interfaces Supported : USB

运动容差 Motion Tolerances : >0.4m/s

解码能力/Symbology Decode Capability

一维条码/1-D: Codabar、Code 39、Code 32 Pharmaceutical (PARAF)、Interleaved 2 of 5、NEC 2 of 5、Code 93、Straight 2 of 5 Industrial、Straight 2 of 5 IATA, Matrix 2 of 5, Code 11、Code 128、GS1-128、UPC-A、UPC-E、EAN/JAN-8、EAN/JAN-13、MSI、GS1 DataBar Omnidirectional、GS1 DataBar Limited、GS1 DataBar Expanded、China Post(Hong Kong 2 of 5)、Korea Post.

二维条码/2-D: Codeblock A、Codeblock F、PDF417、Micro PDF417、GS1 Composite Codes、QR Code、Data Matrix、MaxiCode、Aztec、HANXIN.

默认开启码制: Codabar、Code39、Interleaved2of5、NEC2of5、Code93、Code128、GS1-128、UPC-A、UPC-E0、EAN/JAN-13、EAN/JAN-8、GS1-DataBar、PDF417、QR、DM、Aztec

用户环境参数/User Environment

工作温度 Operating Temperature : -20°C to 60°C

存储温度 Storage Temperature : -30°C to 70°C

湿度 Humidity : 5% to 95% relative humidity, non-condensing

抗震性 Shock Specifications : Designed to withstand 1.2m(5') drops

环境光免疫 Ambient Light Immunity : 0-100,000 Lux.

解码范围/Decode Ranges

Code39(5mil) : 4-20cm

Code39(13mil) : 5-40cm

QR(20mil) : 3-37cm

DM(15mil) : 3-20cm

Performance may be impacted by bar code quality and environmental conditions



手持式二维条码扫描器

HandHeld 2D Barcode Scanner

外观尺寸 (单位 : 毫米) / Dimension (unit: mm)

