

Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PA9T+30%G.F UL94V-0, 颜色: 黑色.

Housing: PA9T+30%G.F UL94V-0, Color: Black

四方针: 黄铜, 镍底30u"MIN, 表面镀高温雾锡

Contact: Brass, HIGH TEMPERATURE MATTE TIN OVER ALL

30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP

Rating Current: 3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.

Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.

温度范围: -40° C to +105° C

Temperture Range: -40° C to +105° C

Ordering Information

P125-11 02 S4 C Z 115 B 1T

HEIGHT OF
HOUSING
25: 2.5mm

NO. OF PINS
PER ROW
1~40P

Contact
Full of Gold
A0=0.8u"
A1=1u"
A2=1.5u"
A3=2u"
A4=3u"
A5=5u"
A6=10u"
A7=15u"
A8=20u"
A9=30u"





Plating
Semi-gold
B0=0.8u"
B1=1u"
B2=1.5u"
B3=2u"
B4=3u"
B5=5u"
B6=10u"
B7=15u"
B8=20u"
B9=30u"

INSULATOR
MATERIAL:
B: PA6T
C: PA9T
D: LCP

LENGTH
OF
TERMINAL

PACKING
A: PE Bag
B: Tape & Reel
C: Tube
D: Tube+CAP
E: Tray

S1=Ordinary Tin Plated
S2=Matte Tin Plated
S3=Tin-plated High-temperature
S4=High Temperature Matte Tin



RoHS
COMPLIANT

客编: V1185

注
意
事
项

1. 带*为品质重点
检验尺寸, 带◇为
SPC管控尺寸

				OPERATION		SCALE		Fit					
				X.X	±0.25	UNIT		MM					
				X.XX	±0.20	SIZE	A4	DESIGN		刘伟 2021.02.02		PART NO.	P125-1102S4CZ115B1T
				X.XXX	±0.10	SHEET		CHECK				TITLE:	2.54排针 1*2P L=11.5/2.8 卧式SMT PA9T DIP:2.8/1.27 镀高温雾锡 CAP+500PCS/卷 V1185
				Angle	±3°	PRQJ.		APPROVE				Customer No.	
				DATE	SYMBOL	MODIFICATION DESCRIPTION							