





P.C.B LAND
DIMENSION

REFERENCE DRAWING

Travel: 0.2 ± 0.1 mm

				TOLERANCE UNLESS SPECIFIED		A2	2022.12.28	更新材质表	WM	
				UP TO 5mm: ± 0.1	ANGULAR	A1	2022.8.15	更新图纸	WM	
				ABOVE 5mm: ± 0.2	$\pm 1^\circ$	NO	DATE	REVISIONS	BY	APPD
5	STEM	LCP/RUBBER	1	WHITE/BLUE	TITLE: TACT SWITCH			UNIT : MM	ROHS	DWN
4	COVER	BRASS	1		MODEL: TS-1188U-D			SCALE: 1:1	COMPLIANT	CHK'D
3	CONTACT	SUS	4	Ag-PLATED	 DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司			APPD		
2	TERMINAL	PHOSPHOR BRONZE	1	Ag-PLATED				PRO.AGL: 		REV :A2
1	BASE	LCP	1	WHITE						
NO.	PART	NAME	MATERIAL	QTY	FINISHING					