



SCHEMATIC



## Specification:

- Rating : DC 50V 0.5A;
- Contact resistance:  $\leq 50m\Omega$   
After test:  $\leq 100m\Omega$
- Insulation resistance:  $\geq 100M\Omega$  (500VDC);  
After test:  $\geq 50M\Omega$
- Withstand voltage: 500VAC ;
- Insertion and extraction force: 5N~30N;
- life test: 5000cycles ;
- Operation temperature range:  $-20^{\circ}\text{C} \sim 70^{\circ}\text{C}$
- Preservative temperature range:  $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$

RECOMMENDED P. C. B. LAYOUT T=1.6  
(TOP VIEW)

					TOLERANCE UNLESS SPECIFIED		DATE	REVISIONS		BY	APPD
					UP TO 5mm: ±0.1	ANGULAR ABOVE 5mm: ±0.2		UNIT : MM	ROHS	DWN	
5	PJ601D CASE	PBT+30GF	1	BLACK			A0	2023.02.09	首次发行	GYW	
4	PJ601D 4# Contact piece	BRASS	1	Sn-PLATED				TITLE: PHONE JACK	UNIT : MM	ROHS	
3	PJ601D 3# Contact piece	BRASS	2	Sn-PLATED				MODEL: PJ-601D	SCALE: 1:1	COMPLIANT	CHK'D
2	PJ601D 2# Spring piece	Phosphor bronze	1	Sn-PLATED						APPD	
1	PJ601D 1# Contact piece	BRASS	2	Sn-PLATED						PRO.AGL:	
NO.	PART	NAME	MATERIAL	QTY	FINISHING						REV :A0



DONGGUANG HAOYU ELECTRONICS CO., LTD  
东莞市弘皓电子有限公司