






## SCHEMATIC

P.C.B LAYOUT  
TOP VIEW

H=1.8MM

## SPECIFICATION

- Rating : DC12V 50mA.
- Contact resistance:  $\leq 100\text{m}\Omega$ .
- Insulation resistance:  $\geq 100\text{M}\Omega$  (DC100V).
- Withstanding voltage: 250VAC .
- Operating Force:  $250\pm 80\text{gf}$
- Travel:  $0.15\pm 0.1\text{mm}$ .
- life test: 10,0000 cycles.
- Operation temperature range:  $-25^\circ\text{C}\sim 85^\circ\text{C}$ .
- Sign "\*" is importance dimension.

NO.	PART	NAME	MATERIAL	QTY	FINISHING	TOLERANCE UNLESS SPECIFIED		NO	DATE	REVISIONS		BY	APPD
						<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°			DWN	CHK'D		
6	STEM	BRASS		1								MLQ	
5	COVER	SUS		1	△								
4	TAPE	PI △		1	YELLOW								
3	CONTACT	SUS		1	Ag-Plated								
2	TERMINAL	BRASS		4	Ag-Plated								
1	HOUSING	LCP		1	BLACK								
						TITLE: TACT SWITCH		UNIT : MM	ROHS	DWN			
						MODEL: TS-1187-018E		SCALE: 1:1	COMPLIANT	CHK'D			
						DONGGUANG HAOYU ELECTRONICS CO., LTD				APPD			
						HOYA 皓宇		东莞市弘皓电子有限公司		PRO.AGL:	□	○	REV :A1