







PAD

RECOMMENDED P.C.B HOLE LAYOUT
COMPONENT SIDE VIEW(TOLERANCE: +/-0.05)

PIN NO.	NAME	YTYPE	DESCRIPTION
1	DAT2	I/O/PP	DATE LINE(BIT2)
2	CD/DAT3	I/O/PP	CARD DETECT DATE LIN(BIT3)
3	CMD	PP	COMMAND RESPONSE
4	VDD	S	SUPPLY VOLTAGE
5	CLX	I	CLOCK
6	VSS	S	SUPPLY VOLTAGE GROUND
7	DAT0	I/O/PP	DATE LINE(BIT0)
8	DAT1	I/O/PP	DATE LINE(DIT1)

Notes:

Electrical Characteristics

Contact Current Rating:0.5A

Dielectric Withstanding Voltage:AC 500V

Insulation Resistance:1000MΩ Min

Contact Resistance:100mΩ Max

Environmental

Temperatrue Range: -40°C TO +85°C

Mechanical Characteristics

Mating Cycles: 5000 Insertions

Insertion/Out Force:0.1-4.0kgf

Material

Insulator: High Temperature Plastic UL94V-0

Color:Black

Contact: Copper Alloy

Shell: Stainless

Spring:SWP

Plating


Contact

Underplate: Nickel 40u".

Contact Area: Gold Flash Over Nickel 40u".

Solder Area: Tin 80u" Min Over Nickel 40u".

Shell:Plate 30u"Nickel Min Over All



MANUFACTURE DWG

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,LtdUNLESS OTHERWISE
SPECIFIED TOLERANCES

TITLE:

TF Push外焊卡座一带自锁

PAR TF-122-CCP9

DWN Lucas

CHKD Ethan

APVD Jacob

SCALE:1:1 UNIT:MM

SIZE:A4 SHEET:1F1

REV:A

DECIMALS:

.X:±0.30


.XX:±0.20

.XXX:±0.10

ANGLES:


X':±2'

CUSTOMER COPY



Direction of use
→

NOTES:

1. Packing quantity per plate: 1000PCS/Plate
2. Loading and packing method



3. Total packaging: 10000PCS/Box



MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: TF Push外焊卡座 一带自锁
DECIMALS:	ANGLES:		PAR TF-122-CCP9
.X:±0.30	X.:±2°		DWN Lucas
.XX:±0.20			CHKD Ethan
.XXX:±0.10			APVD Jacob
CUSTOMER COPY		SCALE 1:1	UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A