








SCHEMATIC




P.C.B LAYOUT



SPECIFICATION

- 1.Rating : DC12V 50mA.
- 2.Contact resistance: $\leq 100\text{m}\Omega$.
- 3.Insulation resistance: $\geq 100\text{M}\Omega$ (DC100V).
- 4.Withstanding voltage: 250VAC .
- 5.Operating Force: $400\pm 100\text{gf}$.
- 6.Travel: $1.3\pm 0.2\text{mm}$.
- 7.Life test: 300,000 cycles.
- 8.Operation temperature range: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.

					TOLERANCE UNLESS SPECIFIED								
7													
6	COVER	PA46	1		<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°	1						
5	TERMINAL	PHOSPHOR BRONZE	1	Ag-Plating			NO	DATE	REVISIONS			BY	APPD
4	HOUSING	PPA	1		TITLE: TACT SWITCH				UNIT : MM	ROHS	DWN		
3	CONTACT	SUS	1	Ag-Plating	MODEL: TC-0031A-H-03				SCALE: 1:1	COMPLIANT	CHK'D		
2	ACTUATOR	SILICONE	1		 DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司						APPD		
1	BUTTON	PPA	1										
NO.	PART	NAME		MATERIAL	QTY	FINISHING				PRO.AGL: 			REV :A0