


1. FIGURE AND DIMENSIONS (视图及尺寸)



针芯性能参数表			
孔位排列	P04	P05	P08
适配线径(AWG)	22AWG	22AWG	22AWG
插合端直径(mm)	1.0	1.0	0.8
额定工作电压 (V)	250V	60V	60V
额定工作电流(A)	4A	4A	2A

Main technical indicators (主要技术指标)	
1. Mating (插拔次数)	5000
2. Working Temperature (温度)	-40~+105°
3. IP Rating (防护级别)	IP 67
4. Diameter of socket end(插合端直径)	See the needle core parameter table/见针芯参数表
5. Rated voltage (额定电压)	See the needle core parameter table/见针芯参数表
6. Rated Current (额定电流)	See the needle core parameter table/见针芯参数表
7. Shell material (壳体材质)	PA66+铜合镀镍/ PA66+ copper nickel plating
8. Pin Material (插针材料)	Pewter bronze gilding(锡青铜镀金)
9. Insulation resistance (绝缘电阻)	> 100MΩ
10. Insulator material (绝缘体材料)	PA66
11. Salt spray test (盐雾测试)	> 72H

Sum up (总结)	
Series (系列)	M12
Shell style/model (外壳样式/型号)	I. AX. TSN: Feed-through connectors/直通型连接器
Button (按键)	1 button(1个按键)
Termination type (终止类型)	Male solder(公焊锡)
Line diameter awg(线材直径)	See the needle core parameter table/见针芯参数表
Cable diameterφ (电缆直径)	-
Match plug (匹配插头)	

版本	TITLE
REVA4	
REVA3	
REVA2	
REVA1	
DRAW	
CHECK	
APPR'D	

DRAWING NO.	REV.
I. AX. TSN. M12. P04. PP7	A0
UNIT	mm
SCALE	Free
SHEET	1 OF N
KKB INDUSTRIAL PRECISION CO., LIMITED	