


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
GP	00		T	REVISED PER ECO-11-020101	10APR2012	CJV CWR



- NOTES:
- 1 FOR MINI-APPLICATOR-12500 PCS REEL.
 - 2 FOR REEL-FEED HAND TOOLING-500 PCS REEL.
 - 3 FOR HAND TOOLING- LOOSE PIECE.
 - 4. MATERIAL: PHOSPHORBRONZE.
 - 5 FINISH:
 - Ni UNDERPLATING ALL OVER.
 - CONTACT AREA PLATING MEETS IEC-807-3 PERFORMANCE LEVEL 2.
 - CRIMP ZONE Sn PLATED.

WIRE RANGE: 28-24 AWG(0,08-0,22mm ²)
INSUL. RANGE: 0,76-1,02 DIA

5	166292-1	5-166052-1	166052-1
FINISH	LOOSE PIECE 3	PART NUMBER 2	PART NUMBER 1
DWN —	09SEP08	 TE Connectivity	
CHK K.MALCZYK	09SEP08		
APVD T.DE BOER	09SEP08	NAME	
PRODUCT SPEC	108-40005	SOCKET CONTACT, SIZE 20 DF.	
APPLICATION SPEC	114-10000		
WEIGHT —	A300779	SIZE	CAGE CODE
CUSTOMER DRAWING	SCALE NTS	DRAWING NO	RESTRICTED TO
		166052	—
		SHEET 1 OF 1	REV T