

RoHS

SPECIFICATIONS

Rated Current:1.5AMP

Contact Resistance:20mΩ Max

Withstand Voltage:500V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40°c to +105°c



Contact Material:Brass

Contact Plating:Au or Sn Over Ni



Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Dimension antitheses list				
ITEM	PB	PW	H	W
001	4.6	6.2	4.3	4.5
002				

OPERATION

DRAW

SCALE

FIT

深圳市连盛精密连接器有限公司

X.X ±0.30

CHECK

UNIT

mm

X.XX ±0.20

APPROVE

SIZE

A4

X.XXX ±0.10

Angle ±3°

DIM TOL

SHEET

1/1

PROJ.

◆

PART NO.

1020200233

TITLE:

2.0FH H=4.3 W=4.5 2x5P SMT=6.2 总高4.6 U型
AU1U 青铜 PA6T

1

2

3

4

5

6

7

8

9