

G

F

E

D

C

B

A

RoHS




SPECIFICATIONS
Rated Current:1.5AMP
Contact Resistance:20mΩ Max
Withstand Voltage:500V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40°c to +105°c

Contact Material:Brass
Contact Plating:Au Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)

				OPERATION		DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司	
				X.X	±0.30					
				X.XX	±0.20	CHECK	UNIT	mm		
				X.XXX	±0.10		SIZE	A4		
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	Angle	±3°	APPROVE	SHEET	1/1	PART NO.	1020200135
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL		PROJECT		TITLE:	2.0FH H4.3mm 2x4pin SMT W4.50

Rated Current:1.5AMP
Contact Resistance:20mΩ Max
Withstand Voltage:500V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40℃ to +105℃

Contact Material: Brass
Contact Plating: Au Over Ni
Insulator Material: Polyester (UL94V-0)
Standard: PA6T
Max. Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)



A					OPERATION		DRAW				SCALE	FIT	深圳市连盛精密连接器有限公司		
					X.X	±0.30					UNIT	mm			
					X.XX	±0.20	CHECK				SIZE	A4	PART NO.	1020200135	
	A0	2018.07.23	NEW DRAWING			X.XXX		±0.10				SHEET			
	REV	DATE	MODIFICATION DESCRIPTION		CHANGE	Angle	±3°	APPROVE				PROJ.		TITLE:	2.0FH H4.3mm 2x4pin SMT W4.50
1		2		3	4		5		6		7		8	9	