

[illegible]

G

F

E

D

C

B

A

RoHS

SPECIFICATIONS
Rated Current:3.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40°c to +105°c

Contact Material:Brass
Contact Plating:Au1U
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230℃ for 30–60 seconds
(260℃ for 10 seconds)

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

2.54xNo.of Positions+0.4±0.3

2.54x(N-1)Positions±0.15

W±0.15

1P 2P

H±0.15

2.54±0.1

0.64x0.4

2.54





φ1.02

2.54x(N-1)Positions

P C ±0.25

Dimension antitheses list						
ITEM	PB	PC	PW	H	W	
001		3.0		8.5	2.5	
002						

				OPERATION		DRAW	SCALE		FIT	深圳市连盛精密连接器有限公司			
				X.X	±0.30		UNIT	mm					
				X.XX	±0.20		SIZE	A4					
				X.XXX	±0.10	SHEET	1 / 1	PART NO.				1020300822	
REV	DATE	MODIFICATION DESCRIPTION		CHANGE	Angle	±3°	APPROVE	PROJECT	TITLE:			2.54FH H=8.5 W=2.5 1*21P DIP PC3.0 Y型 AU1U 青铜 PA6T	
					DIM	TOL							
1	2	3	4	5	6	7	8	9					

[illegible][illegible]