





linear dimension(tolerances Standard GB/T 14486-2008)										—		
variable range	to 6	over 6 to 10	over 10 to 30	over 30 to 60	over 60 to 100	over 100 to 160	over 160 to 10	over 10 to 100	over 100 to 100			
tolerance	±0.20	±0.30	±0.50	±0.70	±1.00	±1.30	±1.60	0.10	0.30	0.60		

REVISION RECORD				
REV.	DESCRIPTION	ECN No.	APPROVED	DATE
A	新发行		CLF	24.08.14

UL/CUL 技术参数					UL/CUL Technical Data							
等级	Use Group	B	C	D								
额定电压	Rated Voltage	V	300	-	300							
额定电流	Rated Current	A	8	-	10							
接线范围	Wire Range					28-16						
单/多芯线	Solid/Stranded	[AWG]										
耐电压	Withstanding Voltage					1600V/1Min						
IEC 技术参数												
IEC Technical Data												
过电压类别	Overvoltage Category	III	III	II								
污染等级	Contamination Class	3	2	2								
额定电压	Rated Voltage	V	-	160	320							
额定电流	Rated Current	A	-	7	7							
额定冲击电压	Impulse withstand voltagea	kV	-	2.5	2.5							
导线截面积	Conductor cross section					1.5						
硬质/柔性导线	Solid/ flexible	[mm²]										
材料		Material										
绝缘材料	Insulation Material	PA66										
阻燃等级	Inflammability	UL94V-0										
导体材料	Conductor Material	铜合金 Copper alloy										
导体表面镀层	Conductive Coating	镀镍 Ni plated										
一般参数		Other Data										
间距 Pitch	[mm]	3.81										
极数 Poles	[P]	3										
剥线长度 Stripping Length	[mm]	7-8										
螺丝 Screw/扭矩 Torque(Max)	[N.m]	M20x2										
工作温度 Operating temperatur	[°C]	-40~+105										
引针尺寸 Pin Dimensions	[mm]	-										
PCB板孔径 PCB Hole Diameter	[mm]	-										



DES.	FGG	DATE	24.08.14	单位 / UNITS	mm	尺寸 / SIZE	A4	比例 / SCALE	1:1	第三视角/THIRD ANGLE PROJECTION	版本 / REV	A
CHK.	CLF	DATE	24.08.14									
APP.	CLF	DATE	24.08.14									
KEFA 慈溪市科发电子有限公司 CXI KEFA ELECTRONIC CO., LTD										名称 / TITLE	KF2EDGK-3.81	