

1

2



3

4

REVISIONS

REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.09	

16.20 [0.638]



规格 Specification:

- 1.额定值 Rating:3A 125/250VAC
- 2.接触电阻 Contact resistance: $\leq 30\text{ m}\Omega$
- 3.绝缘电阻 Insulation resistance: $\geq 100\text{ M}\Omega$ (DC500V/Min)
- 4.电气寿命 Electronics life: > 10000 cycles
- 5.操作力 Operation force: $500\pm 150\text{ gf}$
- 6.所有材料符合Rohs要求 All materials are Rohs compliant

5.50 [0.217]

4.00 [0.157]Travel



3.30 [0.130]

DIN H

PART NO.:

SS-X 03 22 P G-XX N 1 X X
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

- ① SS: 立式拨柄开关;
- ② X: A: 金属外壳;
BLANK: 塑胶外壳;
- ③ 03: 额定值3A;
- ④ 22: 双排两档;
- ⑤ P: 焊板端子;
- ⑥ G: 弧形拨柄;
- ⑦ XX: 拨柄高度H: $3\sim 15\text{mm}$;
- ⑧ N: 方形外壳;
- ⑨ 1: 端子焊脚规格TYPE-1; 2: 端子焊脚规格TYPE-2;
3: 端子焊脚规格TYPE-3; 4: 端子焊脚规格TYPE-4;
5: 端子焊脚规格TYPE-5;
- ⑩ X: 拨柄颜色: B-黑色; W-白色; R-红色
- ⑪ X: 主体颜色: B-黑色; W-白色; R-红色



1.40 [0.055]

4.50 [0.177]

0.50 [0.020]

6.70 [0.264]

9.00 [0.354]

4.50 [0.177]

2.00 [0.079]


6.70 [0.264]

0.80 [0.031]

PCB LAYOUT



产品字码标识



ANGULAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	

DESIGN	桑 葚
CHECKED	
APPROVED	

VIEW:	
UNIT:	mm/in
SIZE:	A4

MODEL TYPE:	SLIDE SWITCH
PART NO.:	SS-0322PG-XXN1XX
DWG NO.:	

XKB INDUSTRIAL PRECISION CO., LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A0

1

2

3

4