







RECOMMENDED PCB LAYOUT(TOP VIEW)
THICKNESS 0.60MM;DEFAULT TOLERANCE:±0.05

PIN NO	SIGNAL NAME	PIN NO	SIGNAL NAME
A1	GND	B12	GND
A2	TXp1	B11	RXp1
A3	TXn1	B10	RXn1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	RXn2	B3	TXn2
A11	RXp2	B2	TXp2
A12	GND	B1	GND

SPECIFICATION

- Rating : 20V DC/AC
Vbus电流5A最大, GND电流5最大,
其他PIN 0.25A最大
- Contact resistance: $\leq 50\text{m}\Omega$.
- Insulation resistance: $\geq 100\text{M}\Omega$ (DC100V).
- Withstanding voltage: 100VAC .
- INSERTION FORCE: 5-20N/ REMOVAL FORCE: 8-20N
- life test: 10000 cycles.
- Operation temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
- Sign"* "is importance dimension.

					TOLERANCE UNLESS SPECIFIED								
					< 1.5: ±0.1mm > 1.5~5.0: ±0.25mm > 5.0: ±0.3mm	ANGULAR ±1°							
5	EMI PLATE	STEEL	1				NO	DATE	REVISIONS			BY	APPD
4	FRONT SHELL	STEEL	1	Ni-PLATED	TITLE: USB JACK			UNIT : MM		ROHS	DWN		
3	MID PLATE	STEEL	1	SN-PLATED	MODEL: USB-307B-B-SU			SCALE: 1:1		COMPLIANT	CHK'D		
2	CONTACTS	BRASS	24	Au-PLATED	 DONGGUANG HAOYU ELECTRONICS CO., LTD 皓宇 东莞市弘皓电子有限公司			APPD					
1	HOUSING	PA9T	1	BLACK									
NO.	PART NAME	MATERIAL	QTY	FINISHING							PRO.AGL:  		REV :A0



DONGGUANG HAOYU ELECTRONICS CO., LTD
东莞市弘皓电子有限公司

PRO.AGL: REV :A0