




SPECIFICATIONS

Current Rating:0.75 Amps

Withstanding Voltage:AC 500V

Insulation Resistance:1000MΩ Min

Contact Resistance:20mΩ Max

Operation Temperature:-40°to+105°

Insrlator Material:Polyester(UL94V-0)

Contact Material:Phosphor bronze

Standard:PA6T

Contact Plating:Gold Flash

Max.Processing Temp:240°C for30-60seconds
(260°C for5seconds)

P/N	PIN	DIM.A	DIM.B
B100UL-WD1P	1	0.00	1.00
B100UL-WD2P	2	1.00	2.00
B100UL-WD3P	3	2.00	3.00
B100UL-WD4P	4	3.00	4.00
B100UL-WD5P	5	4.00	5.00
B100UL-WD6P	6	5.00	6.00
B100UL-WD7P	7	6.00	7.00
B100UL-WD8P	8	7.00	8.00
B100UL-WD9P	9	8.00	9.00
.....			
B100UL-WD40P	40	(PIN-1)	(PIN)

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD									
DIM.	TOL.	TITLE: 1.0FH H2.0 1xnPin SMT W1.5 U型 PC2.8 PB2.3 6T (左前右后)									
X											
X.X	±0.30	DWG. NO.: B100UL-WDNP					DRAWN: MAX				
X.XX	±0.25										
X.XXX	±0.15	PART NO.: B100UL-WDNP					CHECKED: ELLA				
GENERAL	ANGLE:										
	±3°	UNIT: mm					SCALE: none	SHEET: 1 of 1		DWG. SIZE: A4	LAYER: bxconn
											