






SPECIFICATIONS

Current Rating: 1.0 Amps
Withstanding Voltage: AC 500V
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Operation Temperature: -40° to +105°
Insulator Material: Polyester (UL94V-0)
Contact Material: Brass
Standard: PA6T
Contact Plating: Gold Flash
Max. Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)

Part No	Pin	A	B	Part No	Pin	A	B	Part No	Pin	A	B	Part No	Pin	A	B
PZ1.27-UP1D-1A	1	-	-	PZ1.27-UP1D-11A	11	12.70	13.97	PZ1.27-UP1D-21A	21	25.40	26.67	PZ1.27-UP1D-31A	31	38.10	39.37
PZ1.27-UP1D-2A	2	1.27	2.54	PZ1.27-UP1D-12A	12	13.97	15.24	PZ1.27-UP1D-22A	22	26.67	27.94	PZ1.27-UP1D-32A	32	39.37	40.64
PZ1.27-UP1D-3A	3	2.54	3.81	PZ1.27-UP1D-13A	13	15.24	16.51	PZ1.27-UP1D-23A	23	27.94	29.21	PZ1.27-UP1D-33A	33	40.64	41.91
PZ1.27-UP1D-4A	4	3.81	5.08	PZ1.27-UP1D-14A	14	16.51	17.78	PZ1.27-UP1D-24A	24	29.21	30.48	PZ1.27-UP1D-34A	34	41.91	43.18
PZ1.27-UP1D-5A	5	5.08	6.35	PZ1.27-UP1D-15A	15	17.78	19.05	PZ1.27-UP1D-25A	25	30.48	31.75	PZ1.27-UP1D-35A	35	43.18	44.45
PZ1.27-UP1D-6A	6	6.35	7.62	PZ1.27-UP1D-16A	16	19.05	20.32	PZ1.27-UP1D-26A	26	31.75	33.02	PZ1.27-UP1D-36A	36	44.45	45.72
PZ1.27-UP1D-7A	7	7.62	8.89	PZ1.27-UP1D-17A	17	20.32	21.59	PZ1.27-UP1D-27A	27	33.02	34.29	PZ1.27-UP1D-37A	37	45.72	46.99
PZ1.27-UP1D-8A	8	8.89	10.16	PZ1.27-UP1D-18A	18	21.59	22.86	PZ1.27-UP1D-28A	28	34.29	35.56	PZ1.27-UP1D-38A	38	46.99	48.26
PZ1.27-UP1D-9A	9	10.16	11.43	PZ1.27-UP1D-19A	19	22.86	24.13	PZ1.27-UP1D-29A	29	35.56	36.83	PZ1.27-UP1D-39A	39	48.26	49.53
PZ1.27-UP1D-10A	10	11.43	12.70	PZ1.27-UP1D-20A	20	24.13	25.40	PZ1.27-UP1D-30A	30	36.83	38.10	PZ1.27-UP1D-40A	40	49.53	50.80

DIMENSION IN mm		厦门市辛译精密电子有限公司			
TOLERANCE UNLESS OTHERWISE SPECIFIED		Xiamen XinYi Xyconn Electronics Co.,Ltd			
.X±0.35	X.*± 5°	APR.	Alex	TITLE: 1.27PZ H1.0 1xnPin 180° W2.0 PC2.3 PA3.9 PB1.0 L7.2 6T 0.4#	
.XX±0.25	.X*± 3°	CHK.	Jack	DWG NO. PZ1.27-UP1D-NA	
.XXX±0.15	.XX*± 1°	DRA.	Can	PROJ.	CUSTOMER DRAWING
				SIZE A4	SCALE 1:1