



SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~ +85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material: Wafer PA6T UL94-V0(2)
PIN Brass Tin-plated

Circuit	Part No.	Dimensions mm		
		A	B	C
2	HC-PHD-2x2ALT	2.00	6.00	4.80
3	HC-PHD-2x3ALT	4.00	8.00	6.80
4	HC-PHD-2x4ALT	6.00	10.00	8.80
5	HC-PHD-2x5ALT	8.00	12.00	10.80
6	HC-PHD-2x6ALT	10.00	14.00	12.80
7	HC-PHD-2x7ALT	12.00	16.00	14.80
8	HC-PHD-2x8ALT	14.00	18.00	16.80
9	HC-PHD-2x9ALT	16.00	20.00	18.80
10	HC-PHD-2x10ALT	18.00	22.00	20.80
11	HC-PHD-2x11ALT	20.00	24.00	22.80
12	HC-PHD-2x12ALT	22.00	26.00	24.80
13	HC-PHD-2x13ALT	24.00	28.00	26.80
14	HC-PHD-2x14ALT	26.00	30.00	28.80
15	HC-PHD-2x15ALT	28.00	32.00	30.80
16	HC-PHD-2x16ALT	30.00	34.00	32.80
17	HC-PHD-2x17ALT	32.00	36.00	34.80
18	HC-PHD-2x18ALT	34.00	38.00	36.80
19	HC-PHD-2x19ALT	36.00	40.00	38.80
20	HC-PHD-2x20ALT	38.00	42.00	40.80

		GENERAL TOLERANCE	制图 DRAWING	02	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
		DIM TOL	审核 CHECK					
		X.X ±0.30	批准 APPROVAL		产品名称 TITLE	PHD (2.00) 双排立贴	版本 REV.	A
1	初版发行	X.XX ±0.20	比例 SCALE		产品料号 PART NO.	HC-PHD-2xNALT	单位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°	投影 Projection	材料 MATERIAL		页次 SHEET	1/1