


REV.	DESCRIPTION	ECN NO.	NAME	DATE

1




SPECIFICATIONS
 Current Rating:0.75 Amps
 Withstanding Voltage:AC 500V
 Insulation Resistance:1000MΩ Min
 Contact Resistance:20mΩ Max
 Operation Temperature:-40°to+105°
 Insrlator Material:Polyester(UL94V-0)
 Contact Material:Phosphor bronze
 Standard:PA6T
 Contact Plating:Gold Flash
 Max.Processing Temp:240°C for30-60seconds
 (260°C for5seconds)

P/N	PIN	DIM.A	DIM.B
A100UL-WD1P	1	0.00	1.00
A100UL-WD2P	2	1.00	2.00
A100UL-WD3P	3	2.00	3.00
A100UL-WD4P	4	3.00	4.00
A100UL-WD5P	5	4.00	5.00
A100UL-WD6P	6	5.00	6.00
A100UL-WD7P	7	6.00	7.00
A100UL-WD8P	8	7.00	8.00
A100UL-WD9P	9	8.00	9.00
.....
A100UL-WD40P	40	(PIN-1)	(PIN)


2

3




PART NUMBER DESCRIPTION:

A100UL-WDNP



4



RECOMMEND P.C.B LAYOUT
 PCB TOLERANCE:±0.05 (TOP VIEW)

5

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				
DIM.	TOL.	TITLE: 1.0PH H1.0 1xnPin SMT W1.3 PC4.0 PA2.0 PB1.4 L5.0 6T(左前与右前)				
X		DWG. NO.: A100UL-WDNP		DRAWN: MAX		
X.X	±0.30	PART NO.: A100UL-WDNP		CHECKED: ELLA		
X.XX	±0.25	UNIT: mm		APPROVED: WILL		
X.XXX	±0.15	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	
GENERAL ANGLE:	±3°					