





未注公差/General tolerances(mm)

0	>3	>6	>10	>18	>30	>50	>80	>120	>180	>250	>315	>400	>500	0.1/10
~3	~6	~10	~18	~30	~50	~80	~120	~180	~250	~315	~400	~500	~2.50	±2°
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50	



ITEM	NAME OF PART	MATERIAL	NOTES
6	Clapboard	PA66	UL94V-0
5	Small Pin header	Copper alloy	Sn plated
4	Big Pin header	Copper alloy	Sn plated
3	Button	PA66	UL94V-0
2	Cover	PA66	UL94V-0
1	Housing	PA66	UL94V-0
UL 标准/UL Standard:			
额定电压/电流/Rated Voltage(V)/Current(A)		B	C
		300/8	600/8
IEC 标准/IEC Standard:			
过压类别/Overvoltage Category/污染等级/Pollution Degree		III/3	III/2
额定电压/电流/Rated Voltage(V)/Current(A)		500/10	630/10
额定脉冲电压(KV)/Rate Impulse Voltage(KV)		6	6
线径范围(硬线和软线)/Wire Range(rigid and flexible)(mm ² /AWG)		0.2~1.5/22~16	
间距/Pitch(mm)/线数范围/Poles		7.0/N=02~16P	
剥线长度/Stripping length(mm)		8.5~9.5	
使用温度范围/Operating temperature(°C)		-40~+105	
符合RoHS环保要求/Conform to RoHS		Yes	

MATERIAL: /		SURFACE: /	
MAT NO.: /		 宁波高松电子有限公司 NINGBO DEGSON ELECTRICAL CO., LTD	
STATUS: /			
APPD: LiGL 2020.05.23		NAME: DG250-7.0-XXP-1Y-00A(H).	
CHKD: Mek 2020.05.23			
DRFT: LuoXM 2020.05.23		DRAWING NO.: DG250-7.0-C18	
		REV	T1
	SIZE: A4		TYPE: CUSTOMER DRAWING
		SCALE: 4:1	SHEET 1/1