



TYPE(=) 左前右后



SPECIFICATIONS

Current Rating: 1.0 Amps

Withstanding Voltage: AC 500V

Insulation Resistance: 1000MΩ Min

Contact Resistance: 20mΩ Max


Operation Temperature: -40° to +105°

Insulator Material: Polyester (UL94V-0)

Contact Material: Phosphor bronze

Standard: PA6T

Contact Plating: Gold Flash

Max. Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)

Part No	Pin	A	B	Part No	Pin	A	B	Part No	Pin	A	B	Part No	Pin	A	B	Part No	Pin	A	B
PM1.27-UL2D-1A	1	-	-	PM1.27-UL2D-11A	11	12.70	13.97	PM1.27-UL2D-21A	21	25.40	26.67	PM1.27-UL2D-31A	31	38.10	39.37	PM1.27-UL2D-41A	41	50.80	52.07
PM1.27-UL2D-2A	2	1.27	2.54	PM1.27-UL2D-12A	12	13.97	15.24	PM1.27-UL2D-22A	22	26.67	27.94	PM1.27-UL2D-32A	32	39.37	40.64	PM1.27-UL2D-42A	42	52.07	53.34
PM1.27-UL2D-3A	3	2.54	3.81	PM1.27-UL2D-13A	13	15.24	16.51	PM1.27-UL2D-23A	23	27.94	29.21	PM1.27-UL2D-33A	33	40.64	41.91	PM1.27-UL2D-43A	43	53.34	54.61
PM1.27-UL2D-4A	4	3.81	5.08	PM1.27-UL2D-14A	14	16.51	17.78	PM1.27-UL2D-24A	24	29.21	30.48	PM1.27-UL2D-34A	34	41.91	43.18	PM1.27-UL2D-44A	44	54.61	55.88
PM1.27-UL2D-5A	5	5.08	6.35	PM1.27-UL2D-15A	15	17.78	19.05	PM1.27-UL2D-25A	25	30.48	31.75	PM1.27-UL2D-35A	35	43.18	44.45	PM1.27-UL2D-45A	45	55.88	57.15
PM1.27-UL2D-6A	6	6.35	7.62	PM1.27-UL2D-16A	16	19.05	20.32	PM1.27-UL2D-26A	26	31.75	33.02	PM1.27-UL2D-36A	36	44.45	45.72	PM1.27-UL2D-46A	46	57.15	58.42
PM1.27-UL2D-7A	7	7.62	8.89	PM1.27-UL2D-17A	17	20.32	21.59	PM1.27-UL2D-27A	27	33.02	34.29	PM1.27-UL2D-37A	37	45.72	46.99	PM1.27-UL2D-47A	47	58.42	59.69
PM1.27-UL2D-8A	8	8.89	10.16	PM1.27-UL2D-18A	18	21.59	22.86	PM1.27-UL2D-28A	28	34.29	35.56	PM1.27-UL2D-38A	38	46.99	48.26	PM1.27-UL2D-48A	48	59.69	60.96
PM1.27-UL2D-9A	9	10.16	11.43	PM1.27-UL2D-19A	19	22.86	24.13	PM1.27-UL2D-29A	29	35.56	36.83	PM1.27-UL2D-39A	39	48.26	49.53	PM1.27-UL2D-49A	49	60.96	62.23
PM1.27-UL2D-10A	10	11.43	12.70	PM1.27-UL2D-20A	20	24.13	25.40	PM1.27-UL2D-30A	30	36.83	38.10	PM1.27-UL2D-40A	40	49.53	50.80	PM1.27-UL2D-50A	50	62.23	63.50

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd					
TOLERANCE UNLESS OTHERWISE SPECIFIED							
.X±0.35	X.*± 5°	APR.	Alex	TITLE: 1.27PM H4.3 1xNPin SMT W2.1 U型 PC3.5 PB4.6 6T(左前)			
.XX±0.25	.X.*± 3°	CHK.	Jack	DWG NO. PM1.27-UL2D-NA			
.XXX±0.15	.XX.*± 1°	DRA.	Can	PROJ. 		CUSTOMER DRAWING	
				SIZE A4	SCALE 1:1	SHEET 1 / 1	REV. A