


REV.	DESCRIPTION	ECN NO.	NAME	DATE

1





SPECIFICATIONS
 Current Rating:0.75 Amps
 Withstanding Voltage:AC 500V
 Insulation Resistance:1000MΩ Min
 Contact Resistance:20mΩ Max
 Operation Temperature:-40°to+105°
 Insulator Material:Polyester(UL94V-0)
 Contact Material:Phosphor bronze
 Standard:PA6T
 Contact Plating:Gold Flash
 Max.Processing Temp:240°C for30-60seconds
 (260°C for5seconds)


P/N	PIN	DIM.A	DIM.B
A100UP-ZS1P	1	0.00	1.00
A100UP-ZS2P	2	1.00	2.00
A100UP-ZS3P	3	2.00	3.00
A100UP-ZS4P	4	3.00	4.00
A100UP-ZS5P	5	4.00	5.00
A100UP-ZS6P	6	5.00	6.00
A100UP-ZS7P	7	6.00	7.00
A100UP-ZS8P	8	7.00	8.00
A100UP-ZS9P	9	8.00	9.00
.....
A100UP-ZS40P	40	(PIN-1)	(PIN)

2


3



PART NUMBER DESCRIPTION:
 A100UP-ZSNP



4



5

RECOMMEND P.C.B LAYOUT
 PCB TOLERANCE:±0.05 (TOP VIEW)

GENERAL TOLERANCE	DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				
DIM. TOL.	TITLE: 1.0PH H1.0 2xnPin 180度 W2.3 PC2.0 PA2.0 PB1.0 L5.0 6T				
X ±0.30	DWG. NO.: A100UP-ZSNP		DRAWN: MAX		
X.X ±0.25	PART NO.: A100UP-ZSNP		CHECKED: ELLA		
X.XX ±0.15	UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn
X.XXX ±0.15	APPROVED: WILL				
GENERAL ANGLE: ±3°					

