

PS-80 55 S V X- 6P N A

Push Switch

Switch Type
80=8.0×8.0mm

Switch Height
55=5.5mm

Foot Type
S=SMT





Type——
V=Vertical

Attach
A=Base With Pilot
N=No Pilot

Switch Function
L=Lock
N=No Lock

— **Foot Position**
6P=6pin

Operating Force
A=180gf
B=250gf



RECOMMENDED PCB LAYOUT
TOLERANCE:±0.05

7	TERMINAL	BRASS	Ag PLATED
6	CASE	PPA	BLACK
5	LOCK PIN	SUS WIRE	NATURAL
4	SPRING	SUS WIRE	NATURAL
3	CONTACT	BRONZE	Ag PLATED
2	KNOB	PPA	WHITE
1	COVER	PPA	BLACK
NO.	PART NAME	MATERIAL	REMARK



RoHS
Compliant
EU RoHS Standards



SCALE: 1:1	UNIT: mm
SIZE: A4	

Unless otherwise General Tolerance:	
X	±0.40
X.x	±0.30
X.xx	±0.20
X°	±5°
X.x°	±3°

Title: Vertical Tact Switch
SMT 8.0×8.0×H14.3mm

Molde Code: PS-8055SVB-6PNA

DRAWN	CHECKED	APPROVED	DATE
Xia	Chen	Chen	2023.02.01

品赞科技
b-Switch
www.dg-switch.com

REV: A0

SHEET: 1/1