










SPECIFICATION

- 1.Rating : DC 12V 0.3A.
- 2.Function: 2P2T
- 3.Contact resistance: $\leq 100m\Omega$.
- 4.Insulation resistance: $\geq 100M\Omega$ (DC250V).
- 5.Withstanding voltage: 250VAC .
- 6.Operating Force: $250\pm 80gf$ (依客户需求而定) .
- 7.Life test: 10,000 cycles.
- 8.Sign"* "is importance dimension.

				TOLERANCE UNLESS SPECIFIED									
7	TERMINAL	BRASS STRIP	6	Ag PLATED	<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°	AO	2024.5.2	初次发行		TQF		
6	CASE	PPA	1	BLACK			NO	DATE	REVISIONS		BY	APPD	
5	LOCK PIN	SUS WIRE	1										
4	SPRING	SUS WIRE	1										
3	CONTACT	BRONZE	2	Ag PLATED	TITLE: PUSH SWITCH			UNIT : MM	ROHS	DWN			
2	KNOB	PPA	1	WHITE	MODEL: PB-22E81E-S-E-SMT			SCALE: 1:1	COMPLIANT	CHK'D			
1	COVER	PPA	1	WHITE	 皓宇 HAOYU DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司			APPD					
NO.	PART	NAME	MATERIAL	QTY				FINISHING	PRO.AGL: 		REV :A0		