






PUSH



SCHEMATIC



SPECIFICATION

1.Rating : DC 12V 0.3A.

2.Function: 1P2T

3.Contact resistance: $\leq 100m\Omega$.4.Insulation resistance: $\geq 100M\Omega$ (DC250V).

5.Withstanding voltage: 250VAC .

6.Operating Force: 180±80gf (依客户需求而定) .

7.life test: 10,000 cycles.

8.Sign"* "is importance dimension.

9	CONTACTPIECE-2	SUS	1	Ni PLATED	TOLERANCE UNLESS SPECIFIED							
8	CONTACTPIECE-1	SUS	1	Ni PLATED								
7	TERMINAL	BRASS	6	Ag PLATED	<1.5: ±0.1mm	ANGULAR	A0	2024.5.2	初次发行	TQF		
6	CASE	PA66	1	GRAY	>1.5~5.0: ±0.25mm	±1°	NO	DATE	REVISIONS	BY	APPD	
5	LOCK PIN	SUS WIRE	1		>5.0: ±0.3mm							
4	SPRING	SUS WIRE	1		TITLE: PUSH SWITCH			UNIT : MM	ROHS COMPLIANT	DWN		
3	CONTACT	PHOSPHOR BRONZE	3	Ag PLATED	MODEL: PB-12E64-S-C-DD			SCALE: 1:1	CHK'D			
2	KNOB	PBT	1	WHITE	DONGGUANG HAOYU ELECTRONICS CO., LTD 皓宇 东莞市弘皓电子有限公司			APPD				
1	COVER	PPA	1	BLACK								
NO.	PART	NAME	MATERIAL	QTY	FINISHING	PRO.AGL:			REV :A0			