










帽子



SCHEMATIC



P.C.B LAYOUT

技术要求:

1. 使用温度范围:-30~+70℃
2. 耐压:AC500V(50Hz)/min
3. 额定负荷 :DC12V 0.3A
4. 动作力:180±50GF
5. 接触电阻:≤0.03Ω
6. 绝缘电阻 : ≥100MΩ
7. 寿命:10000次

7	PB22E80 HAT	PBT	1	BLACK
6	PB22E80 SPRING	SUS	1	NATURAL
5	PB22E80 CONTACT	PBS	2	Ag PLATING
4	PB22E80 CAM STICK	SUS	1	NATURAL
3	PB22E81 BASE	PA66+30%GF/BRASS	1	BLACK/Ag PLATING
2	PB22E80 COVER	PA66	1	WHITE
1	PB22E80 KNOB	PA66+30%GF	1	BLUE
NO.	PART NAME	MATERIAL	QTY	FINISHING

TOLERANCE UNLESS SPECIFIED								
UP TO 5mm:±0.1	ANGULAR	AO	2016.12.30	首次发行			GYW	
ABOVE 5mm:±0.2	±1°	NO	DATE	REVISIONS			BY	APPD
TITLE: PUSH BUTTON SWITCH			UNIT : MM	ROHS	DWN			
MODEL: PB-22E81-S-C			SCALE: 1:1	COMPLIANT	CHK'D			
 HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司					APPD			
					PRO.AGL:  		REV :A0	