





SPECIFICATIONS

Current Rating: 0.75 Amps
 Withstanding Voltage: AC 500V
 Insulation Resistance: 1000MΩ Min
 Contact Resistance: 20mΩ Max
 Operation Temperature: -40° to +105°
 Insulator Material: Polyester (UL94V-0)
 Contact Material: Phosphor bronze
 Standard: PA6T
 Contact Plating: Gold Flash
 Max. Processing Temp: 240° C for 30-60 seconds
 (260° C for 5 seconds)



TYPE:B (左前右后)



RECOMMEND P. C. B LAYOUT
 PCB TOLERANCE: ±0.05 (TOP VIEW)

TYPE:B (左前右后)



兆星精密电子 (深圳) 有限公司

UNLESS OTHERWISE SPECIFIED TOLERANCE
 X : ±0.30 X° : ±5°
 X.X : ±0.25 X.X° : ±1°
 X.XX : ±0.20 X.XX° : ±0.5°

DRAWN NAME: 1.0FH H2.0 1xnPin SMT W1.5 U型 PC2.8 PB2.3 6T (左前与右前)

SIZE	A4	SCALE	N:1	PROUCT NO.	ZX-PM1.0-1-n*PU-W	
REV	A	UNIT	mm	PROJECT		PAGE 1/1

CHECKED: R R 2023/08/25 CHECKED: / / APPROVED: / /

	of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B
1	0.00	1.00	11	10.00	11.00	21	20.00	21.00	31	30.00	31.00	
2	1.00	2.00	12	11.00	12.00	22	21.00	22.00	32	31.00	32.00	
3	2.00	3.00	13	12.00	13.00	23	22.00	23.00	33	32.00	33.00	
4	3.00	4.00	14	13.00	14.00	24	23.00	24.00	34	33.00	34.00	
5	4.00	5.00	15	14.00	15.00	25	24.00	25.00	35	34.00	35.00	
6	5.00	6.00	16	15.00	16.00	26	25.00	26.00	36	35.00	36.00	
7	6.00	7.00	17	16.00	17.00	27	26.00	27.00	37	36.00	37.00	
8	7.00	8.00	18	17.00	18.00	28	27.00	28.00	38	37.00	38.00	
9	8.00	9.00	19	18.00	19.00	29	28.00	29.00	39	38.00	39.00	
10	9.00	10.00	20	19.00	20.00	30	29.00	30.00	40	39.00	40.00	