




Type A (左前右后)



RECOMMEND P. C. B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

SPECIFICATIONS

- Current Rating: 0.75 Amps
Withstanding Voltage: AC 500V
Insulation Resistance:1000MΩ Min
Contact Resistance: 20mΩ Max
Operation Temperature:-40° to+105°
Insrlator Material: Polyester (UL94V-0)
Contact Material: Brass
Standard: PA6T
Contact Plating: Gold Flash
Max.Processing Temp: 240° C for30-60seconds
(260° C for5seconds)



UNLESS OTHEWIXE SPECIFIED TOLERANCE		DRAWM NAME: 1.0PH H1.0 1xnPin SMT W1.3 PC4.0 PA2.0 PB1.4 L5.0 6T(左前与右前)					
X :±0.30	X° :±5°	SIZE	A4	SCALE	N:1	PROUCT NO.	BX-PZ1.0-1-n*PWZ
X.X :±0.25	X.X° :±1°	REV	A	UNIT	mm	PROJECT	⊕ 
X.XX:±0.20	X.XX° :±0.5°					PAGE	1/1

CHECKED:	L I N	2024/05/10	CHECKED:	/ /	APPROVED:	/ /
----------	-------	------------	----------	-----	-----------	-----

No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B
1	0.00	1.00	11	10.00	11.00	21	20.00	21.00	31	30.00	31.00
2	1.00	2.00	12	11.00	12.00	22	21.00	22.00	32	31.00	32.00
3	2.00	3.00	13	12.00	13.00	23	22.00	23.00	33	32.00	33.00
4	3.00	4.00	14	13.00	14.00	24	23.00	24.00	34	33.00	34.00
5	4.00	5.00	15	14.00	15.00	25	24.00	25.00	35	34.00	35.00
6	5.00	6.00	16	15.00	16.00	26	25.00	26.00	36	35.00	36.00
7	6.00	7.00	17	16.00	17.00	27	26.00	27.00	37	36.00	37.00
8	7.00	8.00	18	17.00	18.00	28	27.00	28.00	38	37.00	38.00
9	8.00	9.00	19	18.00	19.00	29	28.00	29.00	39	38.00	39.00
10	9.00	10.00	20	19.00	20.00	30	29.00	30.00	50	49.00	50.00