



Electrical Characteristics:
 Current rating:0.5A AC/DC
 Voltage rating:50V AC/DC
 Temperature range: -25°C~+85°C
 Withstand Voltage:500V AC/Minute
 Contact Resistance: ≤20mΩ
 Insulation resistance: ≥500MΩ

| 编号 | 尺寸 (mm) | | | |
|----|---------|-------|-------|-------|
| | A | B | C | D |
| 4 | 3.00 | 5.14 | 9.10 | 10.98 |
| 5 | 4.00 | 6.14 | 10.10 | 11.98 |
| 6 | 5.00 | 7.14 | 11.10 | 12.98 |
| 7 | 6.00 | 8.14 | 12.10 | 13.98 |
| 8 | 7.00 | 9.14 | 13.10 | 14.98 |
| 9 | 8.00 | 10.14 | 14.10 | 15.98 |
| 10 | 9.00 | 11.15 | 15.11 | 16.99 |
| 11 | 10.01 | 12.15 | 16.11 | 17.99 |
| 12 | 11.01 | 13.15 | 17.11 | 18.99 |
| 13 | 12.01 | 14.15 | 18.11 | 19.99 |
| 14 | 13.01 | 15.15 | 19.11 | 20.99 |
| 15 | 14.01 | 16.15 | 20.11 | 21.99 |
| 16 | 15.01 | 17.15 | 21.11 | 22.99 |
| 17 | 16.01 | 18.15 | 22.11 | 23.99 |
| 18 | 17.01 | 19.15 | 23.11 | 24.99 |
| 19 | 18.01 | 20.15 | 24.11 | 25.99 |
| 20 | 19.01 | 21.16 | 25.12 | 27.00 |
| 21 | 20.02 | 22.16 | 26.12 | 28.00 |
| 22 | 21.02 | 23.16 | 27.12 | 29.00 |
| 23 | 22.02 | 24.16 | 28.12 | 30.00 |
| 24 | 23.02 | 25.16 | 29.12 | 31.00 |
| 25 | 24.02 | 26.16 | 30.12 | 32.00 |
| 26 | 25.02 | 27.16 | 31.12 | 33.00 |
| 27 | 26.02 | 28.16 | 32.12 | 34.00 |
| 28 | 27.02 | 29.16 | 33.12 | 35.00 |
| 29 | 28.02 | 30.16 | 34.12 | 36.00 |
| 30 | 29.02 | 31.17 | 35.13 | 37.01 |
| 31 | 30.03 | 32.17 | 36.13 | 38.01 |
| 32 | 31.03 | 33.17 | 37.13 | 39.01 |
| 33 | 32.03 | 34.17 | 38.13 | 40.10 |
| 34 | 33.03 | 35.17 | 39.13 | 41.01 |
| 35 | 34.03 | 36.17 | 40.13 | 42.01 |

| 序号 | 名称 | 数量 | 材料 | 附注 |
|----|----|----|-----|---------|
| 1 | 塑件 | 1 | LCP | 本色 |
| 2 | 锁扣 | 1 | LCP | 本色 |
| 3 | 插簧 | N | 磷铜 | 镍底, 高亚锡 |
| 4 | 焊片 | 2 | 磷铜 | 镍底, 高亚锡 |

| ECN BO. | | new | | 2015/5/3 | A | 瀚源 |
|----------|---------|----------|----------------|------------------------|---------------------------------------|-------------|
| DESIGNED | CHECKED | APPROVAL | DRAWING NUMBER | DATE. | REV. | |
| Mikey | Tom | Jerry | | | | |
| | | | PART NAME | 10B26LXX | UNLESS OTHERWISE SPECIFIED,TOLERANCE: | X. ±0.25 |
| | | | MODEL NAME | H-10B26LXX | | X.x ±0.20 |
| | | | 3RD ANGLE PROJ | HanElectricity Co.,LTD | | X.xx ±0.15 |
| | | | | | | ANGULAR ±3° |
| | | | | | | FILE.NO. |