





- NOTES
- 1.CURRENT RATING: 1A.
  - 2.CONTACT RESISTANCE: 100mΩ MAX.
  - 3.INSULATION RESISTANCE: 100MΩ MIN.
  - 4.DIELECTRIC WITHSTANDING: 500V AC MIN.
  - 5.DURABILITY: 5000 CYCLES MIN.
  - 6.CONNECTOR MATING FORCES: 3~30N.
  - 7.CONNECTOR UNMATING FORCES: 3~30NX.
  - 8.SALT SPRAY: 24HOUR
  - 9.WATERPROOF LEVEL: IP67.
  - 10.OPERATING TEMPERATURE: -25°C TO +85°C.
- Not to install the waterproof ring shipment

8F E 5 146 A T A

MODEL DEFINITION  
 Mould Number:01  
 Fixing Method:Fixing Column  
 Interface Method:Convention Extended Opening  
 Overall Length:14.6mm  
 Pin Position:5PIN  
 Mounting Method:SMT  
 Product Series: 3.5mm Audio Jack



ITEM	DESCRIPTION	MATERIAL	QTY	FINSH/COLOR					
F	胶水	环氧树脂	1	黑色				FIRST VIEW	
E	防水圈	硅胶	1	黑色	GENERAL TOLERANCE				
D	底座	高温尼龙	1	黑色	DESIGN	WANGGUIFA	2018.06.12	≥0~2<	±0.15
C	封盖	高温尼龙	1	黑色	CHECKED	ZHENGUILAN	2018.06.12	≥2~5<	±0.25
B	引脚	磷青铜	2.3	镀镍/接触区焊位镀金	APPROVED	LILIANJIANG	2018.06.14	≥0~2<	±0.15
A	引脚	不锈钢	1.4.5	镀镍/接触区焊位镀金				≥5	±0.35

SAMZO COMPONENTS  
 Electronic switch and connector manufacturer

TITLE: :  
 3.5mm 5P SMT JCAK IPX7  
 DWG NO: 8FE5146-P05  
 PART NO: 8FE51461575  
 MODEL NO: 8FE5146ATA  
 NAME:  
 WATERPROOF SOCKET

REV	ECN NO	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	Replace frame			2018.06.12

