


1	2	3	4	5	6	7	8				
				IPX7 1m/30min	ROHS	REV A1	ECN NO NEW	DESCRIPTION Replace frame	DESIGN	APPROVAL	DATE 2018.06.12



3D VIEW



SPECIFICATION:

- CURRENT RATING:DC 0.5A MAX.
- VOLTAGE RATING:DC 12V.
- CONTACT RESISTANCE:50mΩ MAX.
- INSULATION RESISTANCE:100MΩ MIN. AT 500V DC.
- WITHSTANDING VOLTAGE:500V AC FOR 1 MINUTE.
- LIFE TEST:5000 CYCLES MIN,
- MATING FORCE:3~30N,
UNMATING FORCE:3~30N.
- TEPROOF LEVEL: IPX7





Not to install the waterproof ring shipment

8 F E 5 155 A T A


- MODEL DEFINITION
- Mould Number:01
 - Fixing Method:Fixing Column
 - Interface Method:Convention Extended Opening
 - Overall Length:15.5mm
 - Pin Position:5PIN
 - Mounting Method:SMT
 - Product Series: 3.5mm Audio Jack










PLUG MATE DRAWING



(uncompressed)



面板开孔参考尺寸



ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/COLOR			GENERAL TOLERANCE	
D	封盖	高温尼龙	1	黑色			≥0~2<	±0.15
C	底座	高温尼龙	1	黑色	DESIGN	WANGGUIFA	2018.06.12	≥2~5<
B	外壳金属件	磷青铜	1	镀锡	CHECKED	ZHENGUILAN	2018.06.12	≥0~2<
A	引脚	磷青铜	5	镀银/接触面焊点镀金	APPROVED	LILIANJIANG	2018.06.14	≥5

FIRST VIEW

SCALE 1:1 UNIT mm

SAMZO COMPONENTS
Electronic switch and connector manufacturer

The copyright belongs to samzo parts (China) Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts. WWW.KKK-JP.COM

TITLE: 3.5mm SMT JCAK IPX7

DWG NO: 8FE5155-P02

PART NO: 8FE5155002

MODEL NO: 8FE5155ATA

NAME: WATERPROOF SOCKET