







SPECIFICATIONS

Current Rating: 1.5 Amps
 Insulation Resistance: 1000M Ω , Min
 Contact Resistance: 20m Ω , Max
 Withstanding Voltage: AC 500V
 Operation Temperature: -40° to +105°
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester (UL 94V-0)
 Contact Plating: Gold Flash
 Max. Processing Temp: 240° C for 30-60 seconds
 (260° C for 5 seconds)

RECOMMEND P. C. B LAYOUT

PCB TOLERANCE: ± 0.05 (TOP VIEW)



深圳市韩下电子有限公司

UNLESS OTHERWISE SPECIFIED TOLERANCE

X : ± 0.30 X° : $\pm 5^\circ$
 X.X : ± 0.25 X.X° : $\pm 1^\circ$
 X.XX : ± 0.20 X.XX° : $\pm 0.5^\circ$

DRAWN NAME:

HX JN2.0-2x8P TP H5.7

SIZE

A4

SCALE

N:1

PROUCT NO.

REV

A

UNIT

mm

PROJECT

⌀

⌀

PAGE

1/1

DRAWN : 黄彬 2020.6.24

CHECKED :

张伟 2020.6.24

APPROVED :

罗小春 2020.6.24

No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B
6	4.00	6.00	24	22.00	24.00	42	40.00	42.00	60	58.00	60.00
8	6.00	8.00	26	24.00	26.00	44	42.00	44.00	62	60.00	62.00
10	8.00	10.00	28	26.00	28.00	46	44.00	46.00	64	62.00	64.00
12	10.00	12.00	30	28.00	30.00	48	46.00	48.00	66	64.00	66.00
14	12.00	14.00	32	30.00	32.00	50	48.00	50.00	68	66.00	68.00
16	14.00	16.00	34	32.00	34.00	52	50.00	52.00	70	68.00	70.00
18	16.00	18.00	36	34.00	36.00	54	52.00	54.00			
20	18.00	20.00	38	36.00	38.00	56	54.00	56.00			
22	20.00	22.00	40	38.00	40.00	58	56.00	58.00			