







RECOMMEND P. C. B LAYOUT
PCB TOLERANCE: ± 0.05 (TOP VIEW)

SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to $+105^{\circ}$
Contact Material: Brass
Insulator Material: Polyester (UL 94V-0)
Contact plating: Gold Flash
Standard: PA6T
Max. Processing Temp: 240° C for 30-60 seconds
(260° C for 10 seconds)



深圳市韩下电子有限公司

UNLESS OTHERWISE SPECIFIED TOLERANCE

X : ± 0.30 X° : $\pm 5^{\circ}$
X.X : ± 0.25 X.X° : $\pm 1^{\circ}$
X.XX : ± 0.20 X.XX° : $\pm 0.5^{\circ}$

DRAWN NAME:

HX JN2.54-2x7P TP H8.9

SIZE

A4

SCALE

N:1

PROUCT NO.

REV

A

UNIT

mm

PROJECT

⌀

⌀

PAGE

1/1

DRAWNED: 黄彬 2020.11.18

CHECKED:

张伟

2020.11.18

APPROVED:

罗小春

2020.11.18

No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B
6	5.08	7.62	20	22.86	25.40	36	43.18	45.72
8	7.62	10.16	24	27.94	30.48	40	48.26	50.80
10	10.16	12.70	26	30.48	33.02	44	53.34	55.88
12	12.70	15.24	28	33.02	35.56	50	60.96	63.50
14	15.24	17.78	30	35.56	38.10	60	73.66	76.20
16	17.78	20.32	32	38.10	40.64	64	78.74	81.28
18	20.32	22.86	34	40.64	43.18			