





[illegible]

Rated Current:3.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40℃ to +105℃

Contact Material:Brass
Contact Plating: Au Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE ± 0.05)



Dimension antitheses list					
ITEM	PB	PC	PW	H	W
001	9.0		7.1	8.5	5.0
002					

				OPERATION		DRAW			SCALE	FIT	深圳市连盛精密连接器有限公司	
				X.X	±0.30					UNIT		
				X.XX	±0.20	CHECK			SIZE	A4	PART NO.	1020300871
A0	2012.03.28	NEW DRAWING		X.XXX	±0.10					SHEET		
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	Angle	±3°	APPROVE			PROJ.		TITLE:	2.54FH H=8.5 W=5.0 2*22P SMT=7.1 总高9.0 U-A型 AU1U 青铜 PA6T
				DIM	TOL							