

G	RoHS																															
F	SPECIFICATIONS Rated Current:3.0AMP Contact Resistance:20mΩ Max Withstand Voltage:1000V AC/DC Insulation Resistance:1000MΩ Min Operation Temperature:-40℃ to +105℃						Recommended P.C.B Layout(Top Side) (PCB BOARD TOLERANCE±0.05)																									
E	Contact Material:Brass Contact Plating:Au Over Ni Insulator Material:Polyester(UL94V-0) Standard: PA6T Max.Processing Temp: 230℃ for 30-60 seconds (260℃ for 10 seconds)																															
D																																
C																																
B							<table border="1"> <thead> <tr> <th colspan="6">Dimension antitheses list</th></tr> <tr> <th>ITEM</th><th>PB</th><th>PC</th><th>PW</th><th>H</th><th>W</th></tr> </thead> <tbody> <tr> <td>001</td><td>9.0</td><td></td><td>7.1</td><td>8.5</td><td>5.0</td></tr> <tr> <td>002</td><td></td><td></td><td></td><td></td><td></td></tr> </tbody> </table>		Dimension antitheses list						ITEM	PB	PC	PW	H	W	001	9.0		7.1	8.5	5.0	002					
Dimension antitheses list																																
ITEM	PB	PC	PW	H	W																											
001	9.0		7.1	8.5	5.0																											
002																																
A				OPERATION	DRAW		SCALE	FIT	深圳市连盛精密连接器有限公司 PART NO. 1020300867 TITLE: 2.54FH H=8.5 W=5.0 2*17P SMT=7.1 总高9.0 U-A型 AU1U 青铜 PA6T																							
				X.X ±0.30			UNIT	mm																								
				X.XX ±0.20	CHECK		SIZE	A4																								
	A0	2012.03.28	NEW DRAWING	X.XXX ±0.10			SHEET	1/1																								
	REV	DATE	MODIFICATION DESCRIPTION	CHANGE	APPROVE		PROJ.	◆																								
	1	2	3	4	5	6	7	8	9																							

2.54FH H=8.5 W=5.0 2*17P SMT=7.1 总高9.0
U-A型 AU1U 青铜 PA6T