





G	RoHS																																
F	SPECIFICATIONS Rated Current:3.0AMP Contact Resistance:20mΩ Max Withstand Voltage:1000V AC/DC Insulation Resistance:1000MΩ Min Operation Temperature:-40°c to +105°c						Recommended P.C.B Layout(Top Side) (PCB BOARD TOLERANCE±0.05) 																										
E	Contact Material:Brass Contact Plating:Au Over Ni Insulator Material:Polyester(UL94V-0) Standard: PA6T Max.Processing Temp: 230°C for 30-60 seconds (260°C for 10 seconds)																																
D																																	
C																																	
B							<table border="1"> <thead> <tr> <th colspan="6">Dimension antitheses list</th></tr> <tr> <th>ITEM</th><th>PB</th><th>PC</th><th>PW</th><th>H</th><th>W</th></tr> </thead> <tbody> <tr> <td>001</td><td>9.0</td><td></td><td>7.1</td><td>8.5</td><td>5.0</td></tr> <tr> <td>002</td><td></td><td></td><td></td><td></td><td></td></tr> </tbody> </table>			Dimension antitheses list						ITEM	PB	PC	PW	H	W	001	9.0		7.1	8.5	5.0	002					
Dimension antitheses list																																	
ITEM	PB	PC	PW	H	W																												
001	9.0		7.1	8.5	5.0																												
002																																	
A				OPERATION	DRAW		SCALE	FIT	深圳市连盛精密连接器有限公司 PART NO. 1020300869 TITLE: 2.54FH H=8.5 W=5.0 2*19P SMT=7.1 总高9.0 U-A型 AU1U 青铜 PA6T																								
			X.X ±0.30	CHECK			UNIT	mm																									
			X.XX ±0.20				SIZE	A4																									
			X.XXX ±0.10				SHEET	1/1																									
			Angle ±3°	APPROVE			PROJ.																										
	REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL																											
	1	2	3	4	5	6	7	8	9																								

2.54FH H=8.5 W=5.0 2*19P SMT=7.1 总高9.0
U-A型 AU1U 青铜 PA6T

				OPERATION		DRAW			SCALE	FIT
				X.X	±0.30				UNIT	mm
				X.XX	±0.20	CHECK			SIZE	A4
A0	2012.03.28	NEW DRAWING		X.XXX	±0.10				SHEET	1/1
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	Angle	±3°	APPROVE			PROJ.	
				DIM	TOL					