





G	RoHS								G																								
F	SPECIFICATIONS Rated Current:3.0AMP Contact Resistance:20mΩ Max Withstand Voltage:1000V AC/DC Insulation Resistance:1000MΩ Min Operation Temperature:-40℃ to +105℃ Contact Material:Brass Contact Plating:Au Over Ni Insulator Material:Polyester(UL94V-0) Standard: PA6T Max.Processing Temp: 230℃ for 30-60 seconds (260℃ for 10 seconds)								F																								
E									E																								
D									D																								
C	<table border="1"> <thead> <tr> <th colspan="6">Dimension antitheses list</th> </tr> <tr> <th>ITEM</th><th>PB</th><th>PC</th><th>PW</th><th>H</th><th>W</th> </tr> </thead> <tbody> <tr> <td>001</td><td>9.0</td><td></td><td>7.1</td><td>8.5</td><td>5.0</td> </tr> <tr> <td>002</td><td></td><td></td><td></td><td></td><td></td> </tr> </tbody> </table>								Dimension antitheses list						ITEM	PB	PC	PW	H	W	001	9.0		7.1	8.5	5.0	002						C
Dimension antitheses list																																	
ITEM	PB	PC	PW	H	W																												
001	9.0		7.1	8.5	5.0																												
002																																	
B	<table border="1"> <thead> <tr> <th colspan="6">Dimension antitheses list</th> </tr> <tr> <th>ITEM</th><th>PB</th><th>PC</th><th>PW</th><th>H</th><th>W</th> </tr> </thead> <tbody> <tr> <td>001</td><td>9.0</td><td></td><td>7.1</td><td>8.5</td><td>5.0</td> </tr> <tr> <td>002</td><td></td><td></td><td></td><td></td><td></td> </tr> </tbody> </table>								Dimension antitheses list						ITEM	PB	PC	PW	H	W	001	9.0		7.1	8.5	5.0	002						B
Dimension antitheses list																																	
ITEM	PB	PC	PW	H	W																												
001	9.0		7.1	8.5	5.0																												
002																																	
A					OPERATION				SCALE	FIT	深圳市连盛精密连接器有限公司																						
					X.X ±0.30	DRAW			UNIT	mm																							
					X.XX ±0.20	CHECK			SIZE	A4																							
					X.XXX ±0.10				SHEET	1/1																							
	A0	2012.03.28	NEW DRAWING		Angle ±3°	APPROVE			PROJ.	◆	PART NO.	1020300856																					
	REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM TOL						TITLE:	2.54FH H=8.5 W=5.0 2*9P SMT=7.1 总高9.0 U-A型 AU1U 青铜 PA6T																					
	1	2	3	4	5	6	7	8	9																								

<



G

F

E

D

C

B

A

RoHS

SPECIFICATIONS
Rated Current:3.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40°c to +105°c

Contact Material:Brass
Contact Plating:Au Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)

ITEM	PB	PC	PW	H	W
001	9.0		7.1	8.5	5.0
002					

				OPERATION		DRAW			SCALE	FIT	深圳市连盛精密连接器有限公司		
				X.X	±0.30				UNIT	mm			
				X.XX	±0.20	CHECK				SIZE			A4
A0	2012.03.28	NEW DRAWING		X.XXX	±0.10	APPROVE				SHEET			1/1
REV	DATE	MODIFICATION DESCRIPTION		CHANGE	DIM	TOL			PROJ.		TITLE:	2.54FH H=8.5 W=5.0 2*9P SMT=7.1 总高9.0 U-A型 AU1U 青铜 PA6T	

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

1

2

3

4

5

6

7

8

9

[illegible]