

Specifications

Ordering Information

F136-12 15 A0 C MU B 1

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PA9T+30%G.F UL94V-0, 颜色: 黑色.

Housing: PA9T+30%G.F UL94V-0, Color: Black

端子: 磷铜, 镍底30u", 表面镀普金

Contact: Phosphorous, GOLD PLATING OVER ALL
30u" NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电压: 250V AC/DC

Rated Voltage: 250V AC/DC

额定电流: 3 AMP

Rating Current: 3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.


Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.


Withstanding Voltage: AC 500V/Minute.

温度范围: -40° C to +105° C

Temperture Range: -40° C to +105° C



Recommended P.C.B LAYOUT
General Tolerance ±0.05



NO. OF PINS
PER ROW
2-40P

Contact Plating

Full Of Gold

A0=0.8u"

A1=1u"

A2=1.5u"

A3=2u"

A4=3u"

A5=5u"

A6=10u"

A7=15u"

A8=20u"

A9=30u"

S1=Ordinary Tin Plated

S2=Matte Tin Plated

S3=Tin-plated High-temperature

Semi-gold

B0=0.8u"

B1=1u"

B2=1.5u"

B3=2u"

B4=3u"

B5=5u"

B6=10u"

B7=15u"

B8=20u"

B9=30u"

INSULATOR

MATERIAL:

B: PA6T

C: PA9T

D: LCP

PACKING

A: PE Bag

B: Tape & Reel

C: Tube

D: Tube+CAP

E: Tray

RoHS
COMPLIANT

客编: V1169

注意
事项

- 带序号为必检尺寸, 带*为重点检验尺寸
- 保持力0.5kg Min (公司标准)

				OPERATION		SCALE		Fit	Yxcon 广东宇熙新能源技术有限公司			
				X.X	±0.25	UNIT		MM	www.yxcon.com Guangdong Yuxi New Energy Technology Co., Ltd.			
				X.XX	±0.20	SIZE	A4	DESIGN	李官森2024.04.19	PART NO.	F136-1215A0CMUB1	
				X.XXX	±0.10	SHEET	1/1	CHECK		TITLE:	FH2.54*3.6 2415P SMT:7.2 总长38.1 (GRS) U型磷铜 PA9T料 镀普金 CAP+600PCS/卷 V1169	
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM	TOL	PROJ.	Φ	APPROVE	2024.4.19	Customer No.		