

备注(Remark)

1. 材料(MATERIAL)

胶芯: PA9T料+30%G.F UL94V-0, 颜色:黑色.

Housing:PA9T料+30%G.F UL94V-0, Color:Black





端子: 磷铜, 镍底30u"MIN, 表面镀普金

Contact:Phosphorous, GOLD PLATING OVER ALL
30u" MIN NICKEL UNDERPLATING OVER ALL

额定电流: 2 AMP
Rating Current: 2 AMP.
接触阻抗: 20 mΩ MAX.
Contact Resistance: 20 mΩ MAX.
绝缘阻抗: 1000 MΩ MIN.
Insulating Resistance: 1000 MΩ MIN.
耐电压: AC 500V/分钟.
Withstanding Voltage: AC 500V/Minute.
温度范围: -40° C to +105° C
Temperature Range: -40° C to +105° C

F243-12 04 A0 C MU B 1

NO. OF PINS PER ROW	Contact Plating		INSULATOR	PACKING
2-40P	Full Of Gold	Semi-gold	MATERIAL:	A: PE Bag
	A0=0.8u"	B0=0.8u"	B: PA6T	B: Tape & Reel
	A1=1u"	B1=1u"	C: PA9T	C: Tube
	A2=1.5u"	B2=1.5u"	D: LCP	D: Tube+CAP
	A3=2u"	B3=2u"		E: Tray
	A4=3u"	B4=3u"		
	A5=5u"	B5=5u"		
	A6=10u"	B6=10u"		
	A7=15u"	B7=15u"		
	A8=20u"	B8=20u"		
	A9=30u"	B9=30u"		
	S1=Ordinary Tin Plated			
	S2=Matte Tin Plated			
	S3=Tin-plated High-temperature			



Recommended P. C. B LAYOUT
General Tolerance ± 0.05

RoHS
COMPLIANT

客编: V1169

注意

1. 带*为品质重点检验尺寸
2. 保持力0.3kgf Min

				OPERATION		SCALE		Fit		Yxcon 东莞市宇熙精密连接器有限公司 www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.		
				X.X	±0.25	UNIT		MM				
				X.XX	±0.20	SIZE	A4	DESIGN	李官森2023.02.02	PART NO.	F243-1204A0CMUB1	
A0	2023.02.02	/	新版发行	X.XXX	±0.10							
				Angle	±3°	SHEET	1/1	CHECK		TITLE:	FH2.0*4.3 2*4P SMT;6.2 U型磷铜 W=4.5 PA9T 镀普金	
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM	TOL	PROJ.		APPROVE		Customer No.	CAP+800+32/卷 V1169	