

Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PA9T+30%G.F UL94V-0, 颜色: 黑色.

Housing: PA9T+30%G.F UL94V-0, Color: Black

端子: 黄铜, 镍底30u", 表面镀普金

Contact: Brass, GOLD PLATING OVER ALL

30u" NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电压: 250V AC/DC

Rated Voltage: 250V AC/DC

额定电流: 3 AMP

Raring Current: 3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.

Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.

温度范围: -40° C to +105° C

Temperture Range: -40° C to +105° C

Ordering Information

F136-12 06 A0 C MU B 4

NO. OF PINS
PER ROW
2-40P

Contact Plating
Full Of Gold
A0=0.8u"

A1=1u"

A2=1.5u"

A3=2u"

A4=3u"

A5=5u"

A6=10u"

A7=15u"

A8=20u"

A9=30u"

S1=Ordinary Tin Plated

S2=Matte Tin Plated

S3=Tin-plated High-temperature

INSULATOR
MATERIAL:
B: PA6T
C: PA9T
D: LCP

B0=0.8U"

B1=1U"

B2=1.5U"

B3=2U"

B4=3U"

B5=5U"

B6=10U"

B7=15U"

B8=20U"

B9=30U"


PACKING
A: PE Bag
B: Tape & Reel
C: Tube
D: Tube+CAP
E: Tray

RoHS
COMPLIANT



客编: K5005

注意事项

- 带序号为必检尺寸, 带*为重点检验尺寸
- 保持力0.5kg Min (公司标准)



Recommended P.C.B LAYOUT
General Tolerance ±0.05



			OPERATION		SCALE		Fit	Yxcon 广东宇熙新能源技术有限公司		
			X.X	±0.25	UNIT		MM	www.yxcon.com Guangdong Yuxi New Energy Technology Co., Ltd.		
			X.XX	±0.20	SIZE	A4	DESIGN	李官森2024.03.12	PART NO.	F136-1206AOCMUB4
			X.XXX	±0.10	SHEET	1/1	CHECK		TITLE:	2.54排母 3.6mm型高 2*6P SMT:7.2 U型 青铜 PA9T料 镀普金 CAP+800/卷装 K5005
			Angle	±3°	PROJ.		APPROVE	2024.3.12	Customer No.	
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION		DIM	TOL				